

181-15207



Article Number: 181-15207

Slotted Wall Wiring Duct, 1.5" X 2", Non-Adhesive, PVC, Gray, 120ft/Carton



Base Data

Local Order Number 181-15207

Type SL1.5X2

Color Gray (GY)

- Features and Benefits**
- Strong fingers prevent unwanted breaking.
 - Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct.
 - Restricted opening design in the finger of the duct helps keep wires in place.
 - Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Product Description Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "Ts".

Short Description Slotted Wall Wiring Duct, 1.5" X 2", Non-Adhesive, PVC, Gray, 120ft/Carton

Product Dimensions

Length L (imperial) 6.0 ft

Length L (metric) 1.83 m

Width W (imperial) 1.53 "

Width W (metric) 38.86 mm

Width W2 (imperial) 1.5 "

Width W2 (metric) 38.1 mm

Width W3 (imperial) 0.4 "

Width W3 (metric) 10.16 mm

Width W4 (imperial) 1.0 "

Width W4 (metric) 25.4 mm

Width W5 (imperial) 1.62 "

Width W5 (metric) 41.1 mm

Height H (imperial) 2.06 "

Height H (metric) 52.32 mm

Mounting Hole Centers (imperial) 4.0 "

Mounting Hole Centers (metric) 101.6 mm

Logistics and Packaging

Quantity per carton

Package Quantity (imperial) 120 ft

Package Quantity 120

Carton Quantity 120

Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
CSA Certified	Yes
Flammability	self-extinguishing
Operating Temperature	+122 °F (+50 °C)
ROHS Conformity	Yes
Certification / Specification	UL CSA
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No
UL Recognized (US)	Yes