


181-24011



Article Number: 181-24011

Slotted Wall Wiring Duct, 2" X 4", Non-Adhesive, PVC, White, 120ft/Carton

 RoHS

Base Data

Local Order Number	181-24011
Type	SL2X4
Color	White (WH)
Features and Benefits	<ul style="list-style-type: none"><li>• Strong fingers prevent unwanted breaking.</li><li>• Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct.</li><li>• Restricted opening design in the finger of the duct helps keep wires in place.</li><li>• Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.</li></ul>
Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "Ts".
Short Description	Slotted Wall Wiring Duct, 2" X 4", Non-Adhesive, PVC, White, 120ft/Carton

Product Dimensions

Length L (imperial)	6.0 ft
Length L (metric)	1.83 m
Width W (imperial)	2.0 "
Width W (metric)	50.8 mm
Width W2 (imperial)	2.0 "
Width W2 (metric)	50.8 mm
Width W3 (imperial)	0.4 "
Width W3 (metric)	10.16 mm
Width W4 (imperial)	1.0 "
Width W4 (metric)	25.4 mm
Width W5 (imperial)	3.6 "
Width W5 (metric)	91.4 mm
Width W6 (imperial)	0.5 "
Width W6 (metric)	12.7 mm
Height H (imperial)	4.06 "
Height H (metric)	103.1 mm
Mounting Hole Centers (imperial)	4.0 "
Mounting Hole Centers (metric)	101.6 mm

Logistics and Packaging

Quantity per	carton
Package Quantity (imperial)	120 ft

**Package Quantity** 36.6 m

**Carton Quantity** 120

## Material and Specifications

---

**Material** Polyvinylchloride (PVC)

**Material Shortcut** PVC

**CSA Certified** Yes

**Flammability** self-extinguishing

**Operating Temperature** +122 °F (+50 °C)

**ROHS Conformity** Yes

**Certification / Specification** CSA  
UL

**UL Listed (US and Canada)** No

**UL Recognized (US and Canada)** No

**UL Recognized (US)** Yes