



184-15403



Article Number: 184-15403

High Density Slotted Wall Wiring Duct, 1.5" X 4", Non-Adhesive, PVC, White, 120ft/Carton

 RoHS

Base Data

Local Order Number	184-15403
Type	SLHD1.5X4
Color	White (WH)
Features and Benefits	<ul style="list-style-type: none">• Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.• Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.• Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.
Product Description	Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Short Description	High Density Slotted Wall Wiring Duct, 1.5" X 4", Non-Adhesive, PVC, White, 120ft/Carton

Product Dimensions

Length L (imperial)	6.0 ft
Length L (metric)	1.83 m
Width W (imperial)	1.5 "
Width W (metric)	38.1 mm
Width W2 (imperial)	1.5 "
Width W2 (metric)	38.1 mm
Width W3 (imperial)	0.16 "
Width W3 (metric)	4.1 mm
Width W4 (imperial)	0.4 "
Width W4 (metric)	10.2 mm
Width W5 (imperial)	3.6 "
Width W5 (metric)	91.4 mm
Height H (imperial)	4.06 "
Height H (metric)	103.1 mm
Mounting Hole Centers (imperial)	2.0 "
Mounting Hole Centers (metric)	50.8 mm

Logistics and Packaging

Quantity per	carton
Package Quantity (imperial)	120 ft
Package Quantity	120
Carton Quantity	120

Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
CSA Certified	Yes
Flammability	self-extinguishing
Operating Temperature	+122 °F (+50 °C)
ROHS Conformity	Yes
Certification / Specification	CSA UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No
UL Recognized (US)	Yes