

184-23004



Article Number: 184-23004

High Density Slotted Wall Wiring Duct, 2" X 3", Non-Adhesive, PVC, Gray, 120ft/Carton



Base Data

Local Order Number 184-23004

Type SLHD2X3

Color Gray (GY)

- Features and Benefits**
- Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.
 - Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.
 - Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.

Product Description Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

Short Description High Density Slotted Wall Wiring Duct, 2" X 3", Non-Adhesive, PVC, Gray, 120ft/Carton

Product Dimensions

Length L (imperial) 6.0 ft

Length L (metric) 1.83 m

Width W (imperial) 2.02 "

Width W (metric) 51.3 mm

Width W2 (imperial) 2.0 "

Width W2 (metric) 50.8 mm

Width W3 (imperial) 0.16 "

Width W3 (metric) 4.1 mm

Width W4 (imperial) 0.4 "

Width W4 (metric) 10.2 mm

Width W5 (imperial) 2.6 "

Width W5 (metric) 66.0 mm

Width W6 (imperial) 0.5 "

Width W6 (metric) 12.7 mm

Height H (imperial) 3.06 "

Height H (metric) 77.7 mm

Mounting Hole Centers (imperial) 2.0 "

Mounting Hole Centers (metric) 50.8 mm

Logistics and Packaging

Quantity per carton

Package Quantity (imperial) 120 ft

Package Quantity 36.6 m

Carton Quantity 120

Material and Specifications

Material Polyvinylchloride (PVC)

Material Shortcut PVC

CSA Certified Yes

Flammability self-extinguishing

Operating Temperature +122 °F (+50 °C)

ROHS Conformity Yes

Certification / Specification CSA
UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) No

UL Recognized (US) Yes