

184-24004



Article Number: 184-24004

High Density Slotted Wall Wiring Duct, 2" X 4", Non-Adhesive, PVC, Gray, 120ft/Carton



Base Data

Local Order Number	184-24004
Type	SLHD2X4
Color	Gray (GY)
Features and Benefits	<ul style="list-style-type: none">• Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.• Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.• Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.
Product Description	Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Short Description	High Density Slotted Wall Wiring Duct, 2" X 4", Non-Adhesive, PVC, Gray, 120ft/Carton

Product Dimensions

Length L (imperial)	6.0 ft
Length L (metric)	1.83 m
Width W (imperial)	2.0 "
Width W (metric)	50.8 mm
Width W2 (imperial)	2.0 "
Width W2 (metric)	50.8 mm
Width W3 (imperial)	0.16 "
Width W3 (metric)	4.1 mm
Width W4 (imperial)	0.4 "
Width W4 (metric)	10.2 mm
Width W5 (imperial)	3.6 "
Width W5 (metric)	91.4 mm
Width W6 (imperial)	0.5 "
Width W6 (metric)	12.7 mm
Height H (imperial)	4.06 "
Height H (metric)	103.1 mm
Mounting Hole Centers (imperial)	2.0 "
Mounting Hole Centers (metric)	50.8 mm

Logistics and Packaging

Quantity per	carton
Package Quantity (imperial)	120 ft

Package Quantity 36.6 m

Carton Quantity 120

Material and Specifications

Material Polyvinylchloride (PVC)

Material Shortcut PVC

CSA Certified Yes

Flammability self-extinguishing

Operating Temperature +122 °F (+50 °C)

ROHS Conformity Yes

Certification / Specification CSA
UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) No

UL Recognized (US) Yes