


184-32004



Article Number: 184-32004

High Density Slotted Wall Wiring Duct, 3" X 2", Non-Adhesive, PVC, White, 120ft/Carton

 RoHS

Base Data

Local Order Number	184-32004
Type	SLHD3X2
Color	White (WH)
Features and Benefits	<ul style="list-style-type: none"><li>• Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.</li><li>• Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.</li><li>• Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.</li></ul>
Product Description	Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Short Description	High Density Slotted Wall Wiring Duct, 3" X 2", Non-Adhesive, PVC, White, 120ft/Carton

Product Dimensions

Length L (imperial)	6.0 ft
Length L (metric)	1.83 m
Width W (imperial)	3.03 "
Width W (metric)	77.0 mm
Width W2 (imperial)	3.0 "
Width W2 (metric)	76.2 mm
Width W3 (imperial)	0.16 "
Width W3 (metric)	4.1 mm
Width W4 (imperial)	0.4 "
Width W4 (metric)	10.2 mm
Width W5 (imperial)	1.62 "
Width W5 (metric)	41.1 mm
Width W6 (imperial)	1.0 "
Width W6 (metric)	25.4 mm
Height H (imperial)	2.06 "
Height H (metric)	52.3 mm
Mounting Hole Centers (imperial)	2.0 "
Mounting Hole Centers (metric)	50.8 mm

Logistics and Packaging

Quantity per	carton
Package Quantity (imperial)	120 ft

**Package Quantity** 36.6 m

**Carton Quantity** 120

## Material and Specifications

---

**Material** Polyvinylchloride (PVC)

**Material Shortcut** PVC

**CSA Certified** Yes

**Flammability** self-extinguishing

**Operating Temperature** +122 °F (+50 °C)

**ROHS Conformity** Yes

**Certification / Specification** UL  
CSA

**UL Listed (US and Canada)** No

**UL Recognized (US and Canada)** No

**UL Recognized (US)** Yes