

211-60040

Article Number: 211-60040

P Clamp, .39" Width, .26" Max Bundle Dia, .17" Mounting Hole Dia, PA66HS, Black, 1000/pkg



Base Data

Local Order Number	211-60040
Type	H3P
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> • P-Clamps easily guide and locate wire and cables up to 1" in diameter. • Designed with a radiused edge to prevent chaffing and cutting into insulation.
Product Description	HellermannTyton P Clamps easily guide and locate wires and cables. The clamps are designed with a radiused edge to prevent chaffing and cutting into insulation. Available sizes up to 1" bundle diameters.
Fixation Method (FF)	screw-hole
Variant	Closed
Short Description	P Clamp, .39" Width, .26" Max Bundle Dia, .17" Mounting Hole Dia, PA66HS, Black, 1000/pkg

Product Dimensions

Width W (imperial)	0.39 "
Width W (metric)	10.0 mm
Bundle Diameter max (imperial)	0.26 "
Bundle Diameter max (metric)	6.5 mm
Mounting Hole Diameter D (imperial)	0.17 "
Mounting Hole Diameter D (metric)	4.2 mm
Nominal Diameter (imperial)	0.25 "
Nominal Diameter (metric)	6.5 mm
Wall Thickness WT (imperial)	.03937 "
Wall Thickness WT (metric)	1.0 mm
Mounting Hole Centers (imperial)	0.39 "
Mounting Hole Centers (metric)	10.0 mm
Radius R (imperial)	0.04 "
Radius R (metric)	1.0 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	1000 Pieces
Carton Quantity	8000 Pieces
Weight (Metric)	0.4 kg

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
----------	--

Material Shortcut PA66HS
Flammability UL94 V2
Operating Temperature -40 °F to +221 °F (-40 °C to +105 °C)
ROHS Conformity Yes