

211-60140



Article Number: 211-60140

P Clamp, .47" Width, .87" Max Bundle Dia, .2" Mounting Hole Dia, PA66HS, Black, 1000/pkg



Base Data

| | |
|-----------------------|--|
| Local Order Number | 211-60140 |
| Type | H13P |
| Color | Black (BK) |
| Features and Benefits | <ul style="list-style-type: none"> • P-Clamps easily guide and locate wire and cables up to 1" in diameter. • Designed with a radiused edge to prevent chaffing and cutting into insulation. |
| Product Description | HellermannTyton P Clamps easily guide and locate wires and cables. The clamps are designed with a radiused edge to prevent chaffing and cutting into insulation. Available sizes up to 1" bundle diameters. |
| Fixation Method (FF) | screw-hole |
| Variant | Closed |
| Short Description | P Clamp, .47" Width, .87" Max Bundle Dia, .2" Mounting Hole Dia, PA66HS, Black, 1000/pkg |

Product Dimensions

| | |
|-------------------------------------|----------|
| Width W (imperial) | 0.47 " |
| Width W (metric) | 12.0 mm |
| Bundle Diameter max (imperial) | 0.86 " |
| Bundle Diameter max (metric) | 22.0 mm |
| Mounting Hole Diameter D (imperial) | 0.2 " |
| Mounting Hole Diameter D (metric) | 5.2 mm |
| Nominal Diameter (imperial) | 0.87 " |
| Nominal Diameter (metric) | 22 mm |
| Wall Thickness WT (imperial) | .05906 " |
| Wall Thickness WT (metric) | 1.5 mm |
| Mounting Hole Centers (imperial) | 0.81 " |
| Mounting Hole Centers (metric) | 20.5 mm |
| Radius R (imperial) | 0.08 " |
| Radius R (metric) | 2.0 mm |

Logistics and Packaging

| | |
|------------------|-------------|
| Quantity per | bag |
| Package Quantity | 1000 Pieces |
| Carton Quantity | 2000 Pieces |
| Weight (Metric) | 2 kg |

Material and Specifications

| | |
|----------|--|
| Material | Polyamide 6.6 heat stabilized (PA66HS) |
|----------|--|

Material Shortcut PA66HS

Flammability UL94 V2

Operating Temperature -40 °F to +221 °F (-40 °C to +105 °C)

ROHS Conformity Yes