

T120MR9K2



Article Number: 113-12029

Screw Mount Tie, 18lb, 4.3" Long, Max Bun Diameter 4.02", #1/4 Screw, PA66, Natural, 50/pkg

 RoHS

Base Data

Local Order Number	T120MR9K2
Type	T120MR
Color	Natural (NA)
Features and Benefits	• Part design applies easily to any #1/4" Screw • Stud style provides low insertion and high extraction force.
Product Description	Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.
Fixation Method (FF)	fixing hole
Identification Plate Position	none
Mounting Screw Type	M6
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Short Description	Screw Mount Tie, 18lb, 4.3" Long, Max Bun Diameter 4.02", #1/4 Screw, PA66, Natural, 50/pkg

Product Dimensions

Minimum Tensile Strength (imperial)	120.0 lbs
Minimum Tensile Strength (N)	535 N
Length L (imperial)	15.6 "
Length L (metric)	395.0 mm
Width W (imperial)	0.3 "
Width W (metric)	7.6 mm
Height H (imperial)	0.31 "
Height H (metric)	7.9 mm
Bundle Diameter min (imperial)	0.2 "
Bundle Diameter min (metric)	5.0 mm
Bundle Diameter max (imperial)	4.0 "
Bundle Diameter max (metric)	102.0 mm
Mounting Hole Diameter D (imperial)	0.26 "
Mounting Hole Diameter D (metric)	6.5 mm
Thickness T (imperial)	0.07 "
Cable Tie Head Height (Metric)	7.9 mm
Cable Tie Head Length (metric)	28.4 mm
Cable Tie Head Width (metric)	13.4 mm
Cable Tie Head Length (imperial)	1.12 "

Cable Tie Head Width (imperial)	0.51 "
Thickness T (Metric)	1.8 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	50
Carton Quantity	50 Pieces
Weight (Metric)	5.8 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
CSA Certified	No
Flammability	UL94 V2
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes