

TAG5L-105

Article Number: 594-05105

Laser Tag Self-Laminating Label, .8" X .5" X 1.43", 56 Per Sheet, Polyester, White, 5000/pkg



Base Data

Local Order Number TAG5L-105

Type TAG5L

Color White (WH)

- Features and Benefits**
- LaserTags are sheet fed for easy loading and fast printing.
 - LaserTags are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing.
 - LaserTags are printable using toner for long term UV exposure.
 - LaserTags come in a variety of label sizes and types to fit most applications.

Color Marking Field White (WH)

Product Description LaserTags are durable, laser printable labels for applications requiring clear, crisp legibility. The labels are supplied on 8.5" X 11" sheets and are printable using HellermannTyton Tagprint Pro software and a standard laser printer. Specially designed adhesives and materials are used for the LaserTags, ensuring that the labels will not curl, change color, or jam standard laser printers.

For Wire Type 4 Pair UTP / RG6 & RG59 Coax

Paper Format Letter

Short Description Laser Tag Self-Laminating Label, .8" X .5" X 1.43", 56 Per Sheet, Polyester, White, 5000/pkg

Product Dimensions

Length L (imperial) 1.43 "

Length L (metric) 36.4 mm

Core diameter from / to 3.8 - 7.60 mm

Width W (imperial) 0.8 "

Width W (metric) 20.3 mm

Height H (imperial) 0.5 "

Height H (metric) 12.7 mm

Height H2 (imperial) 1.43 "

Height H2 (metric) 36.5 mm

Bundle Diameter min (imperial) 0.149 "

Bundle Diameter min (metric) 3.80 mm

Bundle Diameter max (imperial) 0.29 "

Bundle Diameter max (metric) 7.60 mm

Outside Diameter min. (imperial) 0.15 "

Outside Diameter min. (metric) 3.8 mm

Outside Diameter max. (imperial) 0.29 "

Outside Diameter max. (metric) 7.60 mm

Horizontal Repeat HR (metric) 20.30 mm

Horizontal Repeat HR (imperial)	.800 "
Print Method	Laser
Thickness T (Metric)	35.0 µm
Vertical Repeat VR (imperial)	1.43 "
Vertical Repeat VR (metric)	36.40 mm
Width of Liner WL (imperial)	8.5 "
Width of Liner WL (metric)	215.00 mm

Logistics and Packaging

Quantity per	pc
Package Quantity (imperial)	5000
Package Quantity	5000
Carton Quantity	5000 Pieces
Labels per Column	7
Labels per Row	8
Labels per Sheet	56
Sheets per Pack	90

Material and Specifications

Material	Type 105, Polyester, white (WH)
Material Shortcut	105
Adhesive	Acrylic
Shortcut Adhesive	Acryl
Adhesive Operating Temperature	-40 °F to +302 °F (-40 °C to +150 °C)
Operating Temperature	-40 °F to +300 °F (-40 °C to +149 °C)
ROHS Conformity	Yes