

T120R0HSH4



Article Number: 111-12058

Heavy Duty Cable Tie, 15.2" Long, 120lb Tensile Strength, PA66HS, Black, 500/pkg



Base Data

Local Order Number T120R0HSH4

Type T120R

Color Black (BK)

- Features and Benefits**
- Heat stabilized heavy duty cable ties provide excellent resistance to high heat exposures.
 - Head design provides high tensile strength with very low insertion force.
 - Bent tail ensures a quick and simple installation.

Product Description HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Fixation Method (FF) None

Identification Plate Position none

Releasable Closure (Yes/No) No

Tie Closure plastic pawl

Variant Inside Serrated

Short Description Heavy Duty Cable Tie, 15.2" Long, 120lb Tensile Strength, PA66HS, Black, 500/pkg

Product Dimensions

Minimum Tensile Strength (imperial) 120.0 lbs

Minimum Tensile Strength (N) 535.0 N

Length L (imperial) 15.2 "

Length L (metric) 387.0 mm

Width W (imperial) 0.3 "

Width W (metric) 7.6 mm

Bundle Diameter min (imperial) 0.2 "

Bundle Diameter min (metric) 5.0 mm

Bundle Diameter max (imperial) 4.1 "

Bundle Diameter max (metric) 105.0 mm

Logistics and Packaging

Quantity per bag

Package Quantity 500

Carton Quantity 1000

Material and Specifications

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PA66HS
CSA Certified	No
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40 °F to +257 °F (-40 °C to +125 °C)
ROHS Conformity	Yes
Certification / Specification	UL ZODZ2.E64139 MIL 53421 VG U48/04103
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes