



T5D07500M4



Article Number: 211-00127

P Clamp, .5" Width, .75" Max Bundle Dia, .203" Mounting Hole Dia, PA66, Black, 1000/pkg

 RoHS

Base Data

Local Order Number	T5D07500M4
Type	T5D0750
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none">• Easily guide and locate wire and cables up to 1.5" in diameter.• Designed with a radiused edge to prevent chaffing and cutting into insulation.
Product Description	HellermannTyton P Clamps easily guide and locate wires and cables. The clamps are designed with a radiused edge to prevent chaffing and cutting into insulation. Available sizes up to 1.5" bundle diameters.
Fixation Method (FF)	screw-hole
Variant	Closed
Short Description	P Clamp, .5" Width, .75" Max Bundle Dia, .203" Mounting Hole Dia, PA66, Black, 1000/pkg

Product Dimensions

Width W (imperial)	0.5 "
Width W (metric)	12.7 mm
Bundle Diameter max (imperial)	0.75 "
Bundle Diameter max (metric)	19.05 mm
Mounting Hole Diameter D (imperial)	0.203 "
Mounting Hole Diameter D (metric)	5.1 mm
Wall Thickness WT (imperial)	.050 "
Wall Thickness WT (metric)	1.3 mm
Mounting Hole Centers (imperial)	0.78 "
Mounting Hole Centers (metric)	19.8 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	1000 Pieces

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	Yes
UL Recognized (US and Canada)	Yes

