

TSRP1FW-8A

Article Number: 250-61800

TSRP 0.75", Power Rated Raceway, 8.0 ft Long, PVC, Office White, 160ft/Carton



Base Data

Local Order Number	TSRP1FW-8A
Type	TSRP1-8A
Color	Office White (OEWH)
Features and Benefits	<ul style="list-style-type: none">• Self-locking covers provide taper resistant security, while the hidden positive latch permits quick re-entry access to power cables.• An integrated flexible hinge allows the raceway to endure numerous openings without stress cracking or discoloration.• Raceways and fittings are UL Listed for power up to 600 Volts and meet UL5A and CSA 22.2 Number 62-93 Standards, to insure compliance with local building codes.• Raceway fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.
Product Description	HellermannTyton's TSRP power surface raceway is a one piece, non-metallic, adhesive backed latching raceway designed to aesthetically organize and route either power or communications cables. HellermannTyton offers integrated raceway packages which fit together to meet the requirements of most any raceway application.
Short Description	TSRP 0.75", Power Rated Raceway, 8.0 ft Long, PVC, Office White, 160ft/Carton

Product Dimensions

Length L (imperial)	8.0 ft
Length L (metric)	2.44 m
Width W (imperial)	0.75 "
Width W (metric)	19.05 mm
Height H (imperial)	0.5 "
Height H (metric)	127.0 mm

Logistics and Packaging

Quantity per	box
Package Quantity (imperial)	160
Package Quantity	118.3
Carton Quantity	160

Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
ROHS Conformity	Yes
UL Listed (US)	No

