HellermannTyton

T255M0HIRX2

Article Number: 111-25300

Heavy Duty Cable Tie, 22" Long, 250 lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

RoHS

Base Data

Local Order Number	T255M0HIRX2
Type	T255M
Color	Black (BK)
Features and Benefits	• High impact, heat and UV stabilized heavy duty cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Fixation Method (FF)	None
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Variant	Inside Serrated
Short Description	Heavy Duty Cable Tie, 22" Long, 250 lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Product Dimensions

Minimum Tensile Strength (imperial)	250.0 lbs
Minimum Tensile Strength (N)	1115.0 N
Length L (imperial)	22.0 "
Length L (metric)	560.0 mm
Width W (imperial)	0.5 "
Width W (metric)	12.6 mm
Bundle Diameter min (imperial)	0.49 "
Bundle Diameter min (metric)	12.5 mm
Bundle Diameter max (imperial)	6.3 "
Bundle Diameter max (metric)	160.0 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	25
Carton Quantity	500

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

CSA Certified	No
Flammability	UL94 HB
Operating Temperature	-40 °F to +230 °F (-40 °C to +110 °C)
ROHS Conformity	Yes
Certification / Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

© HellermannTyton 2014