

SNP12AGHS0M4



Article Number: 190-00255

Snapper Hose Clamps, .615"/.721" Min/Max Diameter, PA66GF13%, Black, 1000/pkg

 RoHS

Base Data

Local Order Number	SNP12AGHS0M4
Type	SNP12A
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none">• Designed for quick, ratcheted installation and can be released and reused.• Heat stabilized material is suitable for high temperature applications.
Product Description	HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.
Fixation Method (FF)	Plug-in mounting
Variant	Closed
Short Description	Snapper Hose Clamps, .615"/.721" Min/Max Diameter, PA66GF13%, Black, 1000/pkg

Product Dimensions

Width W min (imperial)	0.825 "
Width W min (metric)	20.96 mm
Width W Max (imperial)	1.177 "
Width W max (metric)	29.9 mm
Width W2 (imperial)	0.233 "
Width W2 (metric)	5.92 mm
Diameter min. (imperial)	0.615 "
Diameter min. (metric)	15.62 mm
Diameter max. (imperial)	0.721 "
Diameter max. (metric)	18.31 mm
Wall Thickness WT (imperial)	.070 "
Wall Thickness WT (metric)	1.78 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	1000
Carton Quantity	4000

Material and Specifications

Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
Material Shortcut	PA66GF13
Flammability	UL94 HB

Operating Temperature -40 °F to +221 °F (-40 °C to +105 °C)

ROHS Conformity Yes