

TAG26T6-100B

Article Number: 596-00009

Thermal Transfer Self-Laminating Label, .5" X .375" X .75" 5 Across, Vinyl, White, 10000/RL



Base Data

Local Order Number	TAG26T6-100B
Type	TAG26T6
Color	White (WH)
Features and Benefits	• HellermannTyton Self-Laminating Labels come on rolls on a standard 3" core for easy loading into a printer or caddy. • Labels are conformable so that they can bend around small gauge wires and tight bends without coming loose over time. • Labels are UL recognized for indoor and outdoor use to expand application options. • HellermannTyton thermal transfer labels work in any thermal transfer printer so that the use always has options to get labels printed without being locked into a single vendor.
Color Marking Field	White (WH)
Product Description	HellermannTyton thermal transfer self-laminating labels are a conformable vinyl film with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels are UL recognized for indoor and outdoor use with an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.
For Wire Type	2 Pair Fiber
Short Description	Thermal Transfer Self-Laminating Label, .5" X .375" X .75" 5 Across, Vinyl, White, 10000/RL

Product Dimensions

Width W (imperial)	0.5 "
Width W (metric)	12.7 mm
Height H (imperial)	0.375 "
Height H (metric)	9.52 mm
Height H2 (imperial)	0.75 "
Height H2 (metric)	19.05 mm
Bundle Diameter min (imperial)	0.059 "
Bundle Diameter min (metric)	1.5 mm
Bundle Diameter max (imperial)	0.118 "
Bundle Diameter max (metric)	3.0 mm
Horizontal Repeat HR (metric)	12.7 mm
Horizontal Repeat HR (imperial)	.5 "
Print Method	Thermal Transfer
Thickness T (Metric)	25 µm
Vertical Repeat VR (imperial)	1.0 "
Vertical Repeat VR (metric)	25.4 mm
Width of Liner WL (imperial)	3.35 "
Width of Liner WL (metric)	85.09 mm

Logistics and Packaging

Quantity per	roll
Package Quantity (imperial)	10000
Package Quantity	10000
Carton Quantity	10000
Labels per Row	6
Weight (Metric)	0.056 kg

Material and Specifications

Material	Type 100, self laminating Vinyl, white (WH)
Material Shortcut	100B
Shortcut Adhesive	Acryl
Adhesive	Acrylic
Adhesive Operating Temperature	-40 °F to +194 °F (-40 °C to +90 °C)
Operating Temperature	-40 °F to +194 °F (-40 °C to +90 °C)
ROHS Conformity	Yes
Certification / Specification	UL-Recognized