



760231449 | SD-1U

Standard Density 1U sliding shelf, accepts (3) LGX/1000 style splice cassettes, modules or panels, providing up to 36 duplex LC ports

Construction Materials

Material Type PC/ABS | Steel

Dimensions

Depth 474.98 mm | 18.70 in
Height 44.45 mm | 1.75 in
Width 482.60 mm | 19.00 in
Weight 6.35 kg | 14.00 lb

Environmental Specifications

Flammability Rating UL 94 V-0

General Specifications

Brand CommScope®
Product Type Modular LGX/1000 style shelf
Rack Units 1
Shelf Movement Sliding
Application Accepts three LGX/1000 footprint panels/cassettes
Color Black
Package Quantity 1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification