



760231456 | SD-2U

Standard Density 2U sliding shelf, accepts (6) LGX/1000 style splice cassettes, modules or panels, providing up to 72 duplex LC ports

Construction Materials

Material Type PC/ABS | Steel

Dimensions

Depth 474.98 mm | 18.70 in
Height 88.90 mm | 3.50 in
Width 482.60 mm | 19.00 in
Weight 7.85 kg | 17.30 lb

Environmental Specifications

Flammability Rating UL 94 V-0

General Specifications

Brand CommScope®
Product Type Modular LGX/1000 style shelf
Rack Units 2
Shelf Movement Sliding
Application Accepts six LGX/1000 footprint panels/cassettes
Color Black
Package Quantity 1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification