



760231498 | SD-4U-FX

**Standard Density 4U fixed shelf, accepts (12) LGX/1000 style footprint modules or panels, providing up to 144 duplex LC ports**

## Construction Materials

Material Type      PC/ABS | Steel

## Dimensions

Depth                485.14 mm | 19.10 in  
Height               177.80 mm | 7.00 in  
Width                482.60 mm | 19.00 in  
Weight               9.30 kg | 20.50 lb

## Environmental Specifications

Flammability Rating      UL 94 V-0

## General Specifications

Brand                    CommScope®  
Product Type            Modular LGX/1000 style shelf  
Rack Units              4  
Shelf Movement        Fixed  
Application              Accepts twelve LGX/1000 footprint panels/cassettes  
Color                    Black  
Package Quantity       1

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2008

### Classification