



Powering Business Worldwide

pe.eaton.com

DA-1 Drive

DA1-342D2FB-A20C

UPC:786685858999

Dimensions:

- **Height:** 9.09 IN
- **Length:** 7.32 IN
- **Width:** 4.21 IN

Weight:3.97 LB

Notes:200-240V 3.0HP 10.5A RFI CONFORMAL COATED See unit nameplate for more detailed approvals.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first. Plus 5 years on capacitor cells.

Specifications:

- **Brake Chopper:** Internal brake chopper
- **Display:** LED
- **Enclosure:** IP20 NEMA 0
- **Frame:** FR2
- **Horsepower:** 1 hp
- **Number Of Inputs:** 5
- **Number Of Outputs:** 2
- **Phase:** Three-phase mains/three-phase motor
- **Protection Filtering:** Internal RFI filter
- **Rated Operational Current:** 2.2A
- **Type:** VF drive
- **User Interface:** RS-485
- **Voltage Rating:** 480V

Supporting documents:

- [Compact solution for your demanding applications - Eaton](#)



- [DA1_A20C\(FR2\) 2D PDF](#)
- [DA1_A20C\(FR2\) 3D Model Xchange](#)
- [PowerXL DA1 Variable Frequency Drives](#)
- [Variable frequency drive - Product overview](#)
- [DA1_A20C\(FR2\) 3D Inventor](#)
- [Eaton Specification Sheet - DA1-342D2FB-A20C](#)
- [Datasheet](#)
- [DA1_A20C\(FR2\) AutoCAD 2D Footprint](#)
- [DA1_A20C\(FR2\) AutoCAD 2D Footprint \(mm\)](#)
- [DA1_A20C\(FR2\) 2D Drawing Xchange](#)

Certifications:

- [UkrSepro](#)
- [EN 60529](#)
- [EN 61800-3](#)
- [EN 61800-5-1](#)
- [UL Listed](#)
- [cUL Certified](#)

Product compliance:

- [C-Tick Compliant](#)
- [RoHS Compliant](#)
- [CE Marked](#)