



Powering Business Worldwide

pe.eaton.com

DS7 Soft Start Controller

DS7-34DSX007N0-D

UPC:786685856315

Dimensions:

- **Height:** 4.05 IN
- **Length:** 5.12 IN
- **Width:** 1.77 IN

Weight:.9 LB

Notes:No internal radio interference suppression filters

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Bypass:** Internal bypass
- **Circuit Breaker Type:** HFD3015
- **Fuse Size:** 15A class RK5 max
- **Control Voltage:** 24 Vdc
- **Environmental Rating:** IP20
- **Frame Size:** Frame 1
- **Horsepower:** 3 hp
- **Phase:** Three-phase mains supply voltage
- **Rated Operational Current:** 7A
- **Series:** Generation 7
- **Voltage Rating:** 480V
- **Wire Type:** SmartWire-DT

Supporting documents:

- [DS7 Series soft start controller](#)
- [DS7 series soft start controllers, Frame 2 \(16-32A\)](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Eaton Specification Sheet - DS7-34DSX007N0-](#)



D

Certifications:

- IEC 60947-4-2
- EN 60947-4-2
- UL Listed
- CSA Certified

Product compliance:

- CE Marked
- C-Tick Compliant