



Powering Business Worldwide

pe.eaton.com

Light Module

SL7-FL24-B

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:0

Warranties: No Data

Specifications:

- **Type:** 70 mm
- **Environmental Rating:** IP66
- **Frequency Rating:** 1.4 Hz
- **Color:** Blue
- **Enclosure:** UL type 4, 4X, 13
- **Illumination:** Strobe LED
- **Quantity:** -1
- **Series:** SL7
- **Voltage Rating:** 24 Vac/Vdc

Supporting documents:

- [Eaton Specification Sheet - SL7-FL24-B](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)

Certifications:

- UL Listed
- cULus Listed
- CSA Certified
- UL 508
- UL Listed file E29184
- CSA Std. C22.2 No. 14-10
- CSA Std. C22.2 No. 94-91
- CSA Class No. NKCR7
- IEC Rated

Product compliance:

- CE Marked



