



Powering Business Worldwide

pe.eaton.com

Light Module

SL7-FL24-R

Dimensions:

- Height: X
- Length: X
- Width: X

Notes:0

Warranties: No Data

Specifications:

- Type: 70 mm
- Environmental Rating: IP66
- Frequency Rating: 1.4 Hz
- Color: Red
- Enclosure: UL type 4, 4X, 13
- Illumination: Strobe LED
- Quantity: -1
- Series: SL7
- Voltage Rating: 24 Vac/Vdc

Supporting documents:

- [Eaton Specification Sheet - SL7-FL24-R](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)

Certifications:

- cULus Listed
- UL Listed
- UL 508
- CSA Certified
- CSA Std. C22.2 No. 14-10
- UL Listed file E29184
- CSA Std. C22.2 No. 94-91
- CSA Class No. NKCR7
- IEC Rated

Product compliance:

- CE Marked



