



31768A

Angle Adapter, standard, 3/8 in tapped hole

Dimensions

Inside Length	22.23 mm		0.88 in
Inside Width	22.23 mm		0.88 in
Outside Length	44.96 mm		1.77 in
Outside Width	49.81 mm		1.96 in

General Specifications

Adapter Type	Angle adapter
Material Type	Stainless steel
Ordering Note	CommScope® standard product in the United States and Canada
Package Quantity	10

Mechanical Specifications

Installation Torque, maximum	15.0 ft lb
Installation Torque, minimum	11.0 ft lb
Material Thickness	4.191 mm 0.165 in
Maximum Loading	Triple stack, 1-5/8 in cable
Mounting	3/8 in tapped hole

Packed Dimensions

Height	14.2 cm		5.6 in
Length	10.2 cm		4.0 in
Shipping Weight	2.33 kg		5.14 lb
Width	14.2 cm		5.6 in

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
China RoHS SJ/T 11364-2006	Below Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

