



7635443-00 | WCS-2

ION®-E Wireless Communications Switch Subrack, 2 U

Product Classification

Brand	ION®
Product Type	Subrack

General Specifications

Brand	ION®
Includes	Fan filter Fan tray
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Rack Type	EIA 19 in

Electrical Specifications

Electrical Safety Standard	EN 60950
Power Consumption	45 W
Voltage Range	12 Vdc

Mechanical Specifications

Mounting	Rack
Slots Available, quantity	11

Environmental Specifications

Operating Temperature	+5 °C to +40 °C (+41 °F to +104 °F)
-----------------------	-------------------------------------

Dimensions

Depth	450.00 mm 17.72 in
Height	88.50 mm 3.48 in
Net Weight	7.60 kg 16.76 lb
Width	482.00 mm 18.98 in

Packed Dimensions

Depth	185.0 mm 7.3 in
Height	522.0 mm 20.6 in
Width	585.0 mm 23.0 in