



7642123-00 | OPT
ION®-E Optical Transport Card

Product Classification

Brand	ION®
Product Type	Card

General Specifications

Brand	ION®
Device Type	Card
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

Electrical Specifications

Power Consumption	8 W
Voltage	12 Vdc

Supervision And Control

General Alarm	Integrated into management system
Management Interface	Integrated into management system

Environmental Specifications

Operating Temperature	+5 °C to +40 °C (+41 °F to +104 °F)
-----------------------	-------------------------------------

Dimensions

Depth	300.00 mm 11.81 in
Height	20.00 mm 0.79 in
Net Weight	0.28 kg 0.62 lb
Width	145.00 mm 5.71 in

Packed Dimensions

Depth	362.0 mm 14.3 in
Height	210.0 mm 8.3 in
Width	63.0 mm 2.5 in