



7642125-00 | SUI  
**ION®-E System User Interface Card**

## Product Classification

Brand	ION®
Product Type	Card

## General Specifications

Brand	ION®
Device Type	Card
Input Connector Interface	RJ45
Input Connector, quantity	3
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

## Electrical Specifications

Power Consumption	2 W
Voltage	12 Vdc

## Supervision And Control

General Alarm	Integrated into management system
Management Interface	Integrated into management system

## Environmental Specifications

Operating Temperature	+5 °C to +40 °C (+41 °F to +104 °F)
-----------------------	-------------------------------------

## Dimensions

Depth	300.00 mm   11.81 in
Height	20.00 mm   0.79 in
Net Weight	0.15 kg   0.33 lb
Width	107.00 mm   4.21 in

## Packed Dimensions

Depth	362.0 mm   14.3 in
Height	210.0 mm   8.3 in
Width	63.0 mm   2.5 in