



7642133-01 | UAP
ION®-E Universal Access Point, 600-2700 MHz

Product Classification

Brand	ION®
Product Type	Access point

General Specifications

Brand	ION®
Input Interface	RJ45
Input, quantity	2
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type	Low

Electrical Specifications

Voltage Range	-60 to -36 Vdc
---------------	----------------

Electrical Specifications Rx (Uplink)

Operating Frequency Band	600 – 2700 MHz
--------------------------	----------------

Electrical Specifications Tx (Downlink)

Operating Frequency Band	600 – 2700 MHz
--------------------------	----------------

Mechanical Specifications

Mounting	Ceiling Wall
RF Antenna Port, quantity	0

Environmental Specifications

Operating Temperature	+5 °C to +40 °C (+41 °F to +104 °F)
-----------------------	-------------------------------------

Dimensions

Depth	105.00 mm 4.13 in
Height	320.00 mm 12.60 in
Net Weight	3.20 kg 7.05 lb
Width	320.00 mm 12.60 in

Packed Dimensions

Depth	388.0 mm		15.3 in
Height	388.0 mm		15.3 in
Width	175.0 mm		6.9 in