

BLK-RCT-A06C0 | 1148446

Fiber Optic Ribbon Breakout Kit, 1-12F/ribbon, 108-216F/tube, 8-11 mm central tube outside dia., 6 tubes/leg

Product Classification

Product Series	BLK-R
Product Type	Fiber breakout kit
Regional Availability	Latin America North America

Body Features

Tubes per Leg	6
---------------	---

Configuration Features

Fibers per Ribbon	1-12
Fibers per Tube	108-216
Number of Breakout Legs	1
Tube Type	Ribbon central tube

Dimensions

Central Tube Outside Diameter	8 – 11 mm .33 – .43 in
Tube Length	5003.8 mm 197.0 in

Operation/Application

Environment	Outdoor
-------------	---------

Other

Breakout Kit Style	Round
--------------------	-------

Product Type Features

Accessory Type	Breakout Kit
Applies To	Ribbon Cable

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant