



DSX-CCW/1000 | X054TX2U2-BG02

DSX1 Copper Cable, category 3, 2 pairs, 5-conductor, 100 Ohm, PVC, 1000 ft

Product Classification

Product Series	DS1
Product Type	Twisted pair cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Jacket Material	PVC
Conductor Material	Tinned copper

Dimensions

Cable Length	305 m 1000 ft
--------------	-----------------

Electrical Specifications

ANSI/TIA Category	3
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1

Environmental Specifications

Operating Temperature	-5 °C to +70 °C (+23 °F to +167 °F)
-----------------------	-------------------------------------

General Specifications

Packaging Type	Reel
Pairs, quantity	2
Cable Component Type	Cross-connect wire
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant