



F4A-PDMDR-2M5-3GSH

FSJ4-50B SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 2.5 m

## OBSOLETE

This product was discontinued on: December 31, 2010

### Replaced By:

F4A-DMDR-P

FSJ4-50B SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, variable length

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	2.500 m   8.202 ft
Specification Sheet Revision Level	A

## Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz			1.11	26.00

F4A-PDMDR-2M5-3GSH

2.2–2.7 GHz			1.08	28.00
698–960 MHz	1.08	28.00		
1700–2200 MHz	1.08	28.00		

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

### Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)



## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4XDM-TU — 7-16 DIN Male for 1/2 in FSJ4-50B cable, factory attached

F4PDR-A — 7-16 DIN Male Right Angle for 1/2 in FSJ4-50B cable, factory attached

SFXDM-TU — 7-16 DIN Male for 1/2 in SFX-500 cable, factory attached

SFXDF-TU — 7-16 DIN Female for 1/2 in SFX-500 cable, factory attached

F4DM-S2 — 7-16 DIN Male for 1/2 in FSJ4-50B cable, factory attached

F4DR-S2 — 7-16 DIN Male Right Angle for 1/2 in FSJ4-50B cable, factory attached

12F450B — 1/2", HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket