



FGS-HTHR-5/8-72 | 4-27051-0845

FiberGuide® Threaded rod, 5/8" diameter, 72" length

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

System Dimensions	100 mm x 100 mm 150 mm x 100 mm 150 mm x 50 mm 4 in x 4 in 6 in x 2 in 6 in x 4 in
Length	1828.8 mm 72.0 in

Environmental Specifications

Flammability Rating	UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel LSZH TCO '99 WEEE
Safety Standard	UL

General Specifications

Product Type	Threaded rod
Color	Silver
Brand	FiberGuide®

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------