

FGS-KTW1-JA | 1438997

FiberGuide® Vertical Duct Kit, slotted hinged cover, 1.5" slot space, 2 in x 2 in, 6 ft length

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

System Dimensions	2 in x 2 in 50 mm x 50 mm
Length	1829.0 mm 6.0 ft

Environmental Specifications

Flammability Rating	UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel LSZH TCO '99 WEEE
Safety Standard	UL

General Specifications

Product Type	Slotted channel with hinged cover
Color	Yellow
Brand	FiberGuide®
Section Type	Vertical section

Mechanical Specifications

Material Type	Acrylnitril Butadien Styrol (ABS)
---------------	-----------------------------------

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------