



FGS-MFTY-50F | 4-29000-7311

FiberGuide® 7/8" Flex Tube, slotted, 50 ft length, yellow

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

Length	15.2 m 50.0 ft
Tube Outer Diameter	22.23 mm 0.88 in

Environmental Specifications

Flammability Rating	UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel LSZH TCO '99 WEEE
Safety Standard	UL

General Specifications

Product Type	Convoluted tube
Color	Yellow
Brand	FiberGuide®
Product Feature	Round
Section Type	Vertical section

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant