

FGS-MH4E-H | 1386131

FiberGuide® 45° Horizontal Elbow, 4 in x 24 in, yellow



- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

System Dimensions	24 in x 4 in		600 mm x 100 mm
Height	120.0 mm		4.7 in
Length	701.0 mm		27.6 in
Width	652.0 mm		25.7 in

Environmental Specifications

Flammability Rating	UL 2024		UL 94 V-0		
Halogen Characteristics	Blue Angel		LSZH		TCO '99 WEEE
Safety Standard	UL				

General Specifications

Section Type	Elbow section
Color	Yellow
Orientation	Horizontal
Angle/Bend Direction	45°
Brand	FiberGuide®
Product Type	Elbow section

Mechanical Specifications

Material Type	Acrylnitril Butadien Styrol (ABS)
---------------	-----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant