



FL1-G7/01GC1-229

FL1000 Fiber Wall Box, SM, SC, 12F soft wall bundle, key lock, 229 meters

Product Classification

Product Series	FL1000
Product Type	Fiber wall box
Regional Availability	North America

Configuration Features

Splice Chip Type	Single fiber heat shrink fusion
Adapter Layout	FC UPC (2), Blank (3)
Loaded 6Pak Adapters	5
Loaded Ports	2
Number of Doors	2
Number of Fibers	12
Number of Locks	1
Number of Positions	12

Dimensions

Cable Length	229.00 m 751.31 ft
Depth	156.97 mm 6.18 in
Height	433.00 mm 17.05 in
Width	511.00 mm 20.12 in

Mechanical Attachment

Mounting Style	Rack-Mount
----------------	------------

Packaging Features

Includes	Cable Clamp (2) Compression Fitting (2) Grounding Kit (2) Tie-Off Adapters (2)
----------	--

Product Type Features

6Pak Type	6-Fiber Soft Wall Bundle
Connector Type	SC
Lock Type	Key Lock
Optical Mode	Singlemode
Wall Box Type	Termination

Regulatory Compliance/Certifications

Product Specifications



FL1-G7/01GC1-229

Agency

RoHS 2011/65/EU

Classification

Compliant