

FL2-12TS350 | 1471057

FL2000 Fiber Termination/Splice Panel, unloaded, 12 Ports, 2RU, 19 in, putty white

Product Classification

Product Series	FL2000
Product Type	Fiber termination/splice panel
Regional Availability	Latin America North America

Body Features

Cable Entry	Front
Cable Exit	Front
Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Access	Front
Number of Ports	12
Configuration	Unloaded

Dimensions

Depth	258.90 mm 10.19 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in

Other

Comment	Left Hinge
---------	------------

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Type Features

Rack Units	2.0
Lock Type	Optional

Usage Conditions

Storage Temperature	-40 – 185 °F -40 – 85 °C
---------------------	----------------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant