

FL2-48SPNL2 | 1150273

FL2000 Fiber Splice Panel, unloaded, for 48 splices, 19 in, 2RU, putty white

Body Features

Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Number of Ports	0
Configuration	Unloaded

Dimensions

Depth	256.540 mm 10.100 in
Height	88.900 mm 3.500 in
Width	482.600 mm 19.000 in

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	Latin America North America
--------	-------------------------------

Product Type Features

Product Type	Fiber Splice Panel
System	FL2000
Rack Units	2.0

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant