

FL2-48TS875 | 1471585

**FL2000 Fiber Termination/Splice Panel, unloaded, 48 Ports, 5RU, 19 in, putty white**

## Product Classification

Product Series	FL2000
Product Type	Fiber termination/splice panel
Regional Availability	Latin America   North America

## Body Features

Cable Entry	Front
Cable Exit	Front
Chassis Color	Putty white
Finish	Powder coated

## Configuration Features

Access	Front
Number of Ports	48
Configuration	Unloaded

## Dimensions

Depth	258.90 mm   10.19 in
Height	222.25 mm   8.75 in
Width	482.60 mm   19.00 in

## Other

Comment	Left Hinge
---------	------------

## Packaging Features

Includes	Installation Instruction   Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

## Product Type Features

Rack Units	5.0
Lock Type	Optional

## Usage Conditions

Storage Temperature	-40 – 185 °F   -40 – 85 °C
---------------------	----------------------------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant