

FL2-96SPNL2 | 1150300

FL2000 Fiber Splice Panel, unloaded, for 96 splices, 19 in, 4RU, putty white

Body Features

Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Number of Ports	0
Configuration	Unloaded

Dimensions

Depth	256.540 mm		10.100 in
Height	177.800 mm		7.000 in
Width	482.600 mm		19.000 in

Packaging Features

Includes	Installation Instruction		Mounting hardware
Packaging Method	Box/Carton		
Packaging Quantity	1		

Product Availability

Region	Latin America		North America
--------	---------------	--	---------------

Product Type Features

Product Type	Fiber Splice Panel
System	FL2000
Rack Units	4.0

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant