

FL2-96TS175 | 1276702

FL2000 Fiber Termination/Splice Panel, unloaded, 96 Ports, 10RU, 19 in, putty white

Body Features

Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Number of Ports	96
Configuration	Unloaded

Dimensions

Depth	256.540 mm		10.100 in
Height	444.500 mm		17.500 in
Width	482.600 mm		19.000 in

Packaging Features

Includes	Installation Instruction		Mounting hardware
Packaging Method	Box/Carton		
Packaging Quantity	1		

Product Availability

Region	Latin America		North America
--------	---------------	--	---------------

Product Type Features

Product Type	Fiber Termination/Splice Panel
System	FL2000
Rack Units	10.0

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant