



FMT-DRT080A00-A24B | 300001750680

FMT Fiber Termination Panel, with sliding tray, 24 LC/UPC, singlemode, 1RU, 19 in, black

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Number of Ports	24
Front Connector Type	LC/UPC
Configuration	Adapters only

Dimensions

Depth	279.908 mm 11.020 in
Height	44.450 mm 1.750 in
Width	482.600 mm 19.000 in

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	Latin America North America
--------	-------------------------------

Product Type Features

Product Type	Fiber Termination Panel
System	FMT
Rack Units	1.0
Optical Mode	Singlemode

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------