



FOSC-400B4-NT-0-NGV | 5822-000

FOSC™400 B4 Fiber Optic Splice Closure, Heat Shrink Cable sealing, no pre-installed trays, ground feedthrough lugs, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Body Features

Cable Seal	Heat Shrink
Color	Black

Configuration Features

Port Shape	Oval (1) and round (4)
Flash Test Valve	Yes
Number of Pre-installed Splice Trays	none
Ground Feedthrough	Yes
Slack Basket	Optional

Dimensions

Closure Diameter	150.000 mm 5.906 in
Length	540.00 mm 21.26 in

Packaging Features

Minimum Order Quantity	1
Packaging Method	Box/Carton

Product Availability

Region	Asia EMEA
--------	-------------

Product Type Features

System	FOSC 400
Product Type	Butt Feeder & Distribution Closure

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------