



FPCA-MMYP009M | 320000102058

**Fiber Optic Patch Cord, singlemode, 1.2 mm OFNP jacket, LC/APC-LC/APC, 9 m, yellow**

- 1.2 mm diameter cable provides a 65% space savings over commonly used 2.0 mm cable
- 1.2 mm diameter fiber patch cords use Reduced Bend Radius (RBR) fiber cable
- Typically used in environments where space constraints and cable routing prove most challenging

## Product Classification

Product Type	Fiber patch cord, simplex
Regional Availability	Latin America   North America
Product Series	FPCA

## Body Features

Connector Color (End A)	Green
Connector Color (End B)	Green

## Configuration Features

Number of Connectors (End A)	1
Number of Connectors (End B)	1

## Construction Materials

Jacket Color	Yellow
Total Fibers, quantity	1

## Dimensions

Assembly Length	9.00 m   29.53 ft
Cable Outer Diameter	1.2 mm

## Industry Standards

Approved Standards	GR-326 CORE   GR-409   GR-449-CORE   IEC 61754-4   TIA-604-3-B
Flammability Rating	OFNP (Plenum) Jacket

## Product Type Features

Connector Type (End A)	LC/APC
Connector Type (End B)	LC/APC
Fiber Type	OS1
Fiber Diameter	9/125 µm
Optical Mode	Singlemode

## Signal Characteristics

Insertion Loss (Max)	0.40 dB
Return Loss (Min)	-65 dB

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---