



L4A-DMDF-1M-P

LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Female, 1 m

General Specifications

| | |
|------------------------------------|--------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | LDF4-50A |
| Interface, Connector A | 7-16 DIN Male |
| Interface, Connector B | 7-16 DIN Female |
| Nominal Size | 1/2 in |
| Length | 1.000 m 3.281 ft |
| Specification Sheet Revision Level | A |

Electrical Specifications

| | |
|----------------------------------|---------------------------|
| 3rd Order IMD Static | -159.00 dBc -116.00 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| DTF, Connector A | -34.00 dB |
| DTF, Connector B | -34.00 dB |

Jumper Assembly Sample Label



Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz | 1.06 | 30.00 |
| 1700–2200 MHz | 1.06 | 30.00 |
| 2200–2700 MHz | 1.11 | 26.00 |

L4A-DMDF-1M-P

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

ISO 9001:2008

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)

Designed, manufactured and/or distributed under this quality management system



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4DM-S2 — 7-16 DIN Male for 1/2 in LDF4-50A cable, factory attached

L4DF-S2 — 7-16 DIN Female for 1/2 in LDF4-50A cable, factory attached

LDF4-50A-2T — LDF4-50A-2T, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

12L450 — 1/2", HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket