



L4A-PDMDM-1M-3GSH

LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1 m

## OBSOLETE

This product was discontinued on: December 31, 2010

### Replaced By:

|               |   |
|---------------|---|
| L4A-DMDM-3-P  | LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 3 ft. |
| L4A-DMDM-1M-P | LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1 m   |

## General Specifications

|                                    |                    |
|------------------------------------|--------------------|
| Body Style, Connector A            | Straight           |
| Body Style, Connector B            | Straight           |
| Cable Family                       | LDF4-50A           |
| Interface, Connector A             | 7-16 DIN Male      |
| Interface, Connector B             | 7-16 DIN Male      |
| Nominal Size                       | 1/2 in             |
| Length                             | 1.000 m   3.281 ft |
| Specification Sheet Revision Level | A                  |

## Electrical Specifications

|                  |             |
|------------------|-------------|
| 3rd Order IMD    | -116.00 dBm |
| DTF, Connector A | -34.00 dB   |
| DTF, Connector B | -34.00 dB   |

## Jumper Assembly Sample Label



## Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
|----------------|------|------------------|

L4A-PDMDM-1M-3GSH

|               |      |       |
|---------------|------|-------|
| 698–960 MHz   | 1.06 | 30.00 |
| 1700–2200 MHz | 1.06 | 30.00 |

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

### Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)



## Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4XDM-DT — 7-16 DIN Male for 1/2 in LDF4-50A cable, factory attached

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

CX-10D-SA — HELIAX® Low Density Foam Coaxial Cable, corrugated copper, black PE jacket, special marking "SWCC  
SHOWA CX-10D-SA ANDREW HELIAX® 1/2" LDF4-50A"

LDF4-50A-2T — LDF4-50A-2T, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

12L450 — 1/2", HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket