



## L4A-PDMDM-2M-3GSH

**LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 2 m**

### **OBSOLETE**

**This product was discontinued on: December 31, 2010**

#### **Replaced By:**

L4A-DMDM-6-P	LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 6 ft.
L4A-DMDM-2M-P	LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 2 m
L4A-DMDM-3M-P	LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 3 m
L4A-DMDM-4M-P	LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 4 m
L4A-DMDM-5M-P	LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 5 m
L4A-DMDM-2M5-P	LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 2.5 m
L4A-DMDM-3M5-P	LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 3.5 m

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	2.000 m   6.562 ft
Specification Sheet Revision Level	A

## Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

## Jumper Assembly Sample Label

L4A-PDMDM-2M-3GSH



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.06	30.00
1700–2200 MHz	1.06	30.00

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)



## Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4XDM-DT — 7-16 DIN Male for 1/2 in LDF4-50A cable, factory attached

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

CX-10D-SA — HELIAX® Low Density Foam Coaxial Cable, corrugated copper, black PE jacket, special marking "SWCC SHOWA CX-10D-SA ANDREW HELIAX® 1/2" LDF4-50A"

LDF4-50A-2T — LDF4-50A-2T, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

12L450 — 1/2", HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket