



L4A-PDMDR-1M5-3GSH

LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 1.5 m

**OBSOLETE**

This product was discontinued on: March 1, 2011

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	1.500 m   4.921 ft
Specification Sheet Revision Level	A

## Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

## Jumper Assembly Sample Label

**Batch** 0123456789 | **Manufacturing Date** (two digit year and week) US22 | 1240 | **Product Revision** /A  
**Manufacturing Plant** US22 | **Product Revision** /A  
**Part Number** F4-DMDM-2M-D  
 2 M (6.562 FT)  
 SUREFLEX ASSEMBLY  
 U.S. PATENT 5802710  
 Product of UNITED STATES  
**Serial Number** 12US220001242

## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.08	28.00
1700–2200 MHz	1.08	28.00

## Regulatory Compliance/Certifications

L4A-PDMDR-1M5-3GSH

**Agency**

RoHS 2011/65/EU  
China RoHS SJ/T 11364-2006  
ISO 9001:2008

**Classification**

Compliant by Exemption  
Above Maximum Concentration Value (MCV)  
Designed, manufactured and/or distributed under this quality management system



## Included Products

---

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4PDR-DT — 7-16 DIN Male Right Angle for 1/2 in LDF4-50A cable, factory attached

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

CX-10D-SA — HELIAX® Low Density Foam Coaxial Cable, corrugated copper, black PE jacket, special marking "SWCC SHOWA CX-10D-SA ANDREW HELIAX® 1/2" LDF4-50A"

LDF4-50A-2T — LDF4-50A-2T, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

12L450 — 1/2", HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket