

MX6-TMD2L00 | 1346131

**OMX Fiber Termination Block, 144 FC/UPC, singlemode, putty white, left oriented**

## Body Features

Chassis Color	Putty white
Finish	Powder coated

## Configuration Features

Number of Ports	144
Front Connector Type	FC/UPC
Configuration	Adapters only

## Dimensions

Depth	283.210 mm		11.150 in
Height	373.000 mm		14.685 in
Width	203.200 mm		8.000 in

## Operation/Application

For Use With	OMX Frames
--------------	------------

## Packaging Features

Includes	Installation Instruction		Mounting hardware
Packaging Method	Box/Carton		
Packaging Quantity	1		

## Product Availability

Region	EMEA		Latin America		North America
--------	------	--	---------------	--	---------------

## Product Type Features

Product Type	Fiber Termination Block
System	OMX
Optical Mode	Singlemode

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant