

MX6-TMD2R00 | 1346155

OMX Fiber Termination Block, 144 FC/UPC, singlemode, putty white, right oriented

Body Features

Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Number of Ports	144
Front Connector Type	FC/UPC
Configuration	Adapters only

Dimensions

Depth	283.210 mm 11.150 in
Height	373.000 mm 14.685 in
Width	203.200 mm 8.000 in

Operation/Application

For Use With	OMX Frames
--------------	------------

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	EMEA Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Fiber Termination Block
System	OMX
Optical Mode	Singlemode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant